3.9 BeamCheck[™] - Beam profiling system for Additive Manufacturing

- Beam check measures:
 - Focal spot size at the build plane
 - Laser power at the build plane
 - Laser power density at the build plane
 - Changes in spot size & power density over time
- 0.1 to 600 Watt integrated power sensor
- For fiber lasers; 1060 to 1080nm Wavelength
- Power densities to >3MW/cm²
- Spot sizes 37um to 3.5mm
- Frame rate multiple frames per second
- Additive manufacturing system focal length 200mm >400mm

Additive manufacturing has restructured how prototype, developmental and advanced design mechanical components are made. Direct Laser Melting, Selective Laser Sintering or 3D metal Printing is quickly becoming the standard for designs that could not be fabricated with traditional metal removing techniques.



To create consistent, strong structures using laser-based additive manufacturing processes that meet flyable DOD standards or FDA requirements, the metallurgy must be consistent, and a laser beam of known dimension, power density and focal spot location is required.

Quality 3D laser printed processes require a laser delivering the correct amount of power, distributed correctly and focused at the correct location. To insure consistent and structurally sound parts these parameters should be directly measured before and after any critical part is made.

BeamCheck is an integrated laser measurement system designed to measure critical laser beam parameters for laser-based additive manufacturing systems BeamCheck includes a CCD camera for spatial measurements and a NIST-traceable power sensor that will provide a complete analysis of the laser power density profile.

The camera is precisely located at the build plane so that an accurate power density model of the working laser beam can be made. A beam splitter directs a small percentage of the beam to the camera, while the majority of the beam is directed to the integrated power sensor. From these measurements an accurate beam spot size and power density can be derived.


G 10	_		naseye i Nakalang ki Baneti kan se Celondy kalakatan bekang bertir kanasa ki 1936 bijeta 🖉 🖉 🗙
and Bardinging &	ad an in the second		the terms and the
Resulta Resultance Full Fairner 1		. 18	Otaligs (*Disaber)
Name	Value	Aber	
# Powerfarmers			
Total Power	127.69	W	
Avg Pwr Density 190	2 997 888 97	W/cm ²	
Peak Fluence 150	6.005.646.63	W/cm ²	计算法 化化合理 医马克尔氏 化合理 医子宫 机合成 化合理合理 化合理合理
# Spotal-		1000	
D4am ^{IID}	69.14	um.	
DKE 10/90	73.89	um	
D%pk	72.80	um	
D%t	51.88	um.	
Ellipticity 110	0.90		
Doergeron - Gaunian -			
H Tapilai *			
Eff Avg Fluence mo	850.214.40	W/cm ²	The June Power 127 for William Control of the Power of Control of
ii Topelato"	000.514.40		Diel 10199 7389 an Ang fwir Desawy 2007 888 97 W/cm ⁻¹ Highsay 00
Comment	Average power		Highlight Q 20
10-domaine+	Conclusion Brenning		Average power density at the work surface is SMW/cm *2
10 TopHat *			Average upon size at the work surface in Plum
Designity have -			
			I FERRES/II STAFARASINE TYPESCHERASISSIAN ATTAC VOM INNEL SECOND STAFARASINA AND

თ. თ

BeamCheck Includes

Ophir[®]

Model	BeamCheck
Beam Profiling	
	SP928 high resolution CCD camera
	3.69um square pixel, USB 3.0, multiple frames per second
	CCD is positioned within +/- 50µm of the same distance as the work surface
	LBS-300-NIR laser beam splitter / attenuator
	Directs the beam to both the camera and power sensor
Power Measurement	
	FL600A-LP2-65 laser power sensor
	NIST traceable, 600 Watts, fan cooled
	JUNO Smart Sensor to USB Adapter
Software	
	BeamGage Professional Software to run on user supplied PC
	StarLab software to interface power sensor to BeamGage
Data is saved in ASCII and HDI	-5 formats
Custom print-out includes;	
	2D False Color Power Density Map
	Total Power
	NIST/National Lab Traceable certificate
	Beam Diameter (D4sigma, 90/10 Knife Edge, Power-in-a-Bucket)
	Peak Power Density
Calibration Certificates for;	
	FL600A-LP2-65 Power Sensor
	JUNO USB Converter
	SP928 CCD Camera
	Calibration of build plate distance to camera array location
Compliance	CE, UKCA, China RoHS
Ordering Information	
Part Number	SP90411



<u>З.</u>0